

# Elastic

Elastic Resin for Soft Flexible Parts

\$199 / L

Our softest Engineering Resin, this 50A Shore durometer material is suitable for prototyping parts normally produced with silicone. Choose Elastic Resin for parts that will bend, stretch, compress, and hold up to repeated cycles without tearing.

Wearables and consumer goods prototyping

Medical models and devices

Compliant features for robotics

Special effects props and models



FLELCL01

**formlabs** 

**Prepared** 01 . 07 . 2019  
**Rev** 01 01 . 07 . 2019

To the best of our knowledge the information contained herein is accurate. However, Formlabs, Inc. makes no warranty, expressed or implied, regarding the accuracy of these results to be obtained from the use thereof.

# Material Properties Data

	METRIC <sup>1</sup>		IMPERIAL <sup>1</sup>		METHOD
	Green	Post-Cured <sup>2</sup>	Green	Post-Cured <sup>2</sup>	
Ultimate tensile strength <sup>3</sup>	1.61 MPa	3.23 MPa	234 psi	468 psi	ASTM D 412-06 (A)
Stress at 50% elongation	.92 MPa	.94 MPa	133 psi	136 psi	ASTM D 412-06 (A)
Stress at 100% elongation	1.54 MPa	1.59 MPa	223 psi	231 psi	ASTM D 412-06 (A)
Elongation at Failure <sup>3</sup>	100%	160%	100%	160%	ASTM D 412-06 (A)
Compression set at 23C for 22 hrs	2%	2%	2%	2%	ASTM D 395-03 (B)
Compression set at 70C for 22 hrs	3%	9%	3%	9%	ASTM D 395-03 (B)
Tear strength <sup>4</sup>	8.9 kN/m	19.1 kN/m	51 lbf/in	109 lbf/in	ASTM D 624-00
Shore hardness	40A	50A	40A	50A	ASTM 2240

<sup>1</sup>Material properties can vary with part geometry, print orientation, print settings and temperature.

<sup>2</sup>Data was obtained from parts printed using Form 2, 100 µm, Elastic settings, washed in Form Wash for 20 minutes and postcured with Form Cure at 60C for 20 minutes.

<sup>3</sup>Tensile testing was performed after 3+ hours at 23 °C, using a Die C dumbbell and 20 in/min cross head speed.

<sup>4</sup>Tear testing was performed after 3+ hours at 23 °C, using a Die C tear specimen and a 20 in/min cross head speed

## Solvent Compatibility

Percent weight gain over 24 hours for a printed and post-cured 1 x 1 x 1 cm cube immersed in respective solvent:

Mechanical Properties	24 hr size gain (%)	24 hr weight gain (%)	Mechanical Properties	24 hr size gain (%)	24 hr weight gain (%)
Acetic Acid, 5 %	<1	2.8	Hydrogen Peroxide (3 %)	<1	2.2
Acetone	19.3	37.3	Isooctane	<1	3.5
Isopropyl Alcohol	13.3	25.6	Mineral Oil, light	<1	<1
Bleach, ~5 % NaOCl	<1	2	Mineral Oil, heavy	<1	<1
Butyl Acetate	18.2	39.6	Salt Water (3.5 % NaCl)	<1	1.7
Diesel	1.2	4.2	Sodium hydroxide (0.025 %, pH = 10)	<1	2
Diethyl glycol monomethyl ether	12	28.6	Water	<1	2.3
Hydrolic Oil	<1	2.1	Xylene	20.4	46.6
Skydrol 5	9.9	21.7	Strong Acid (HCl Conc)	14.2	39.4